



NOTES

- 1). THE FLOWMETER MUST BE INSTALLED LEVEL TO WITHIN ±1°.
- 2). FOR SENSING PLATE REMOVAL, CLEARANCE OF 914 mm (36") ABOVE THE TOP COVER IS REQUIRED.
- 3). FOR FURTHER INFORMATION REFER TO THE MILLTRONICS MILLFLO INSTRUCTION MANUAL OR CONTACT YOUR SIEMENS MILLTRONICS REPRESENTATIVE.

USE DIMENSIONS ONLY - DO NOT SCALE		0	FOR RELEASE	RPC	RDC	MAR 17/04
DIMENSIONS ARE IN MILLIMETERS		Rev.	Revision / ECN Description	Drawn	Appr.	Date
Third Angle Projection 	Product Group	Tolerance Unless Otherwise Noted: UOS		Scale:	Size:	
	MASS DYNAMICS	1 Place Decimal ± 0.8 Angles: ± 0.5°		.0625=1	B	
For Public Release	Date:	17 MAR 2004		TITLE: 300 mm (12") MILLTRONICS MILLFLO 60°, C/W DIN FLANGE CUSTOMER OUTLINE DRAWING		
	Drawn:	R. CLYSDALE				
	Checked:	P. RICCI				
	Approved:	R. CLOSS				
	Location:	PETERBOROUGH				
	SIEMENS MILLTRONICS PROCESS INSTRUMENTS INC. Peterborough, Ontario, Canada	DRAWING No:	23650459	Rev.	0	
	File No. 2365045900	Plot at:	1=16	Sheet	1 Of 1	

1
2
3
4
5
6
7
8
9
10